

Datasheet

Donkey Anti-Mouse IgG (H&L) secondary antibody (Texas Red)

Catalog Number: PAB10743

Regulation Status: For research use only (RUO)

Product Description: Donkey anti-mouse IgG recognizes mouse IgG whole molecule. This secondary antibody was purified using antigen affinity chromatography. The antibody is conjugated with Texas Red.

Immunogen: Mouse IgG whole molecule

Host: Donkey

Reactivity: Mouse

Applications: Flow Cyt, IF
(See our web site product page for detailed applications information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Conjugation: Texas Red™

Purification: This product was prepared from monospecific antiserum by immunoaffinity chromatography, followed by solid phase adsorption(s) to remove any unwanted reactivities.

Concentration: 2.0 mg/mL

Conjugation Note: 7.1 moles Texas Red™ per mole of donkey IgG

Recommend Usage: The optimal working dilution should be determined by the end user.

Storage Buffer: In 10 mM potassium phosphate, 75 mM NaCl, 50% (v/v) glycerol, pH 7.2 (0.01% (w/v) sodium azide, 10 mg/mL BSA (Immunoglobulin and Protease free))

Storage Instruction: Store at 4°C. For long term

storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

References:

1. Texas Red, a hydrophilic, red-emitting fluorophore for use with fluorescein in dual parameter flow microfluorometric and fluorescence microscopic studies. Titus JA, Haugland R, Sharrow SO, Segal DM. J Immunol Methods. 1982;50(2):193-204.