prosci-inc.com

ProSci Incorporated
12170 Flint Place
Poway, CA 92064


Toll Free: +1 (888) 513 9525
Local: +1 (858) 513 2638
Fax: +1 (858) 513 2692

techsupport@prosci-inc.com

HIGH PERFORMANCE ANTIBODIES ... AND MORE

ZNF609 Antibody

CATALOG NUMBER: 27-401



Antibody used in WB on Human Brain lysate at 1.25 ug/ml.

Specifications

SPECIES REACTIVITY:	Human, Rat
TESTED APPLICATIONS:	ELISA, WB
APPLICATIONS:	ZNF609 antibody can be used for detection of ZNF609 by ELISA at 1:1562500. ZNF609 antibody can be used for detection of ZNF609 by western blot at 1.25 ug/mL, and HRP conjugated secondary antibody should be diluted 1:50,000 - 100,000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
POSITIVE CONTROL:	1) Cat. No. XBL-10123 - Fetal Brain Tissue Lysate
PREDICTED MOLECULAR WEIGHT:	155 kDa
IMMUNOGEN:	Antibody produced in rabbits immunized with a synthetic peptide corresponding a region of human ZNF609.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Antibody is purified by protein A chromatography method.
PHYSICAL STATE:	Lyophilized
BUFFER:	Antibody is lyophilized in PBS buffer with 2% sucrose. Add 100 uL of distilled water. Final antibody concentration is 1 mg/mL.
CONCENTRATION:	1 mg/ml
STORAGE CONDITIONS:	For short periods of storage (days) store at 4˚C. For longer periods of storage, store ZNF609 antibody at -20˚C. As with any antibody avoid repeat freeze-thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	ZNF609, KIAA0295
ACCESSION NO.:	NP_055857
PROTEIN GI NO.:	71725360

OFFICIAL SYMBOL:	ZNF609
GENE ID:	23060

Background

BACKGROUND:	The function of ZNF609 remains unknown.
REFERENCES:	1) Oh, J.H., et al., (2005) Mamm. Genome 16 (12), 942-954.

FOR RESEARCH USE ONLY

December 12, 2016